



1080p HDR-Studio-Kamerasystem

AK-HC3900

Die Studiokamera AK-HC3900GJ/HC3900GSJ wurde speziell für den Broadcast-Bereich sowie für die Übertragung von Veranstaltungen konzipiert und ist mit einem großen Sensor für hohe Empfindlichkeit und eine ausgezeichnete Videoqualität ausgestattet.

Key Features

Verfügt über einen großen 4K-MOS-Sensor und überzeugt durch eine hohe Empfindlichkeit von F10 (2000 lx) und die rauscharmen Aufnahmen dank des Signal-Rausch-Verhältnisses von 62 dB (im Hochempfindlichkeitsmodus)

Ausgestattet mit CAC (Chromatic Aberration Compensation), Schräglagenreduktion und DRS-Funktionen (Dynamic Range Stretch)

Mit zweifachem Digital Extender

Unterstützt standardmäßig HDR/BT.709 im HD-Modus und HDR/BT.2020 im 4K-Modus

Das 4K-Upgrade ermöglicht die Ausgabe von 4K-Videos mit einer horizontalen Auflösung von 2000 TV-Zeilen



AK-HC3900

<https://eu.connect.panasonic.com/ch/de/broadcast-proav/studio-cameras/ak-hc3900>

General -> Power Supply	DC 12 V (when using an external power supply)
	DC 190 V (when AK-HCU250PJ/HCU250PSJ/HCU250EJ/ HCU250ESJ is connected)
General -> Power Consumption	82 W (maximum, when connecting to an external 12 V and including supply to an externally connected devices)
	92 W (maximum, when AK-HCU250PJ/HCU250PSJ/HCU250EJ/ HCU250ESJ is connected and including supply to an externally connected devices)
General -> Operating Temperature	-10 °C to 45 °C (14 °F to 113 °F)
	(Preheating required under a temperature 0°C (32 °F) or below)
General -> Operating Humidity	85% or less (relative humidity)
General -> Storage Temperature	-20 °C to 60 °C (-4 °F to 140 °F)
General -> Weight	Approx. 4.0 kg (8.80 lbs.) (body only, excluding the accessories)
General -> Dimensions	W 151 mm x H 267 mm x D 369 mm
	(5-31/32 inches x 10-17/32 inches x 14-17/32 inches) (excluding protrusions)
Camera Unit -> Pickup Device	11.14 million pixels, MOS Sensor
Camera Unit -> Optical Filter -> ND	Clear, 1/4, 1/16, 1/64
Camera Unit -> Lens Mount	2/3-type bayonet
Camera Unit -> Sensitivity	wo shooting modes
	[HIGH SENS] F10 (59.94 Hz)/F11 (50 Hz)
	[NORMAL] F6 (59.94 Hz)/F7 (50 Hz) 2000 lx, 3200 K, when white reflectivity is 89.9%
Camera Unit -> Horizontal Resolution	-2000 TV lines or above (center, when using AK-HUC01)
	> 4K
Camera Unit -> Horizontal Resolution	-1000 TV lines or above (center)
	> HD
Camera Unit -> S/N	62 dB or above
Camera Unit -> Horizontal Modulation	50% or above (27.5 MHz)
Camera Unit -> Gain Switching -> HIGH SENS	-6, -3, 0, 3, 6, 9, 12, 15, 18, 21, 24, 27, 30, 33, 36
Camera Unit -> Gain Switching -> NORMAL	-6, -3, 0, 3, 6, 9, 12, 15, 18, 21, 24, 27, 30, 33, 36
Camera Unit -> Shutter Speed -> [59.94i]/[59.94p] mode	1/100, 1/120, 1/125, 1/250, 1/500, 1/1000, 1/1500, 1/2000
Camera Unit -> Shutter Speed -> [50i]/[50p] mode	1/60, 1/100, 1/125, 1/250, 1/500, 1/1000, 1/1500, 1/2000
Camera Unit -> Shutter Speed -> [29.97p] mode	1/48, 1/50, 1/60, 1/96, 1/100, 1/120, 1/125, 1/250, 1/500, 1/1000, 1/1500, 1/2000
Camera Unit -> Shutter Speed -> [25p] mode	1/48, 1/50, 1/60, 1/96, 1/100, 1/125, 1/250, 1/500, 1/1000, 1/1500, 1/2000
Camera Unit -> Shutter Speed -> [23.98p] mode	1/48, 1/50, 1/60, 1/96, 1/100, 1/120, 1/125, 1/250, 1/500, 1/1000, 1/1500, 1/2000
Camera Unit	1920 x 1080/59.94p/50p/29.97p/25p/23.98p
	*when using AK-HUC01
	3840 x 2160/59.94p/50p/29.97p/25p/23.98p
Video Input/Output - > < HD-SDI1 > Terminal	BNC x 1
	3G/1.5G-SDI: 0.8 V [p-p], 75 Ω
Video Input/Output - > < HD-SDI2 > Terminal	BNC x 1
	3G/1.5G-SDI: 0.8 V [p-p], 75 Ω

Video Input/Output - > < AUX > Terminal	BNC x 1
	Functions as terminal/ terminal by switching the setting in the menu
	: 3G/1.5G-SDI: 0.8 V [p-p], 75 Ω
	: VBS signal 1 V [p-p], 75 Ω
Audio Input/Output - > < MIC 2 > Terminal	XLR x 1, 3-pin (female)
	// switchable
	: 0 dBu
	: -60 dBu, -40 dBu, or -20 dBu menu can be selected
Audio Input/Output - > < MIC > Terminal (front)	XLR x 1, 3-pin (female)
	// switchable
	: 0 dBu
	: -60 dBu, -40 dBu, or -20 dBu menu can be selected
Intercom - > < INTERCOM1 > Terminal	XLR x 1, 5-pin, female type
Other Input/Output - > < OPT FIBER > Terminal	Optical composite connector x 1
Other Input/Output - > < LENS > Terminal	12-pin x 1
Other Input/Output - > < VF > Terminal	20-pin x 1
Other Input/Output - > < VF > Terminal (rear)	29-pin x 1
Other Input/Output - > < DC IN > Terminal	XLR x 1, 4-pin, DC 12 V
Other Input/Output - > < LAN > Terminal	RJ-45 x 1